

15BG100 8Ω


LF Drivers - 15.0 Inches




- 2000 W continuous program power capacity
- 100 mm (4 in) copper voice coil
- 35 1000 Hz response
- 94.5 dB sensitivity
- FEA optimized Neodymium magnet assembly
- Aluminium demodulating ring for very low distortion
- Double silicone spider with optimized compliance
- Ventilated voice coil gap for reduced power compression



LF Drivers- 15.0 Inches





SPECIFICATIONS

Nominal Diameter	380 mm (15.0 in)
Nominal Impedance	8 Ω
Minimum Impedance	6.0 Ω
Nominal Power Handling ¹	1000 W
Continuous Power Handling ²	2000 W
Sensitivity ³	94.5 dB
Frequency Range	35 - 1000 Hz
Voice Coil Diameter	100 mm (4.0 in)
Winding Material	Copper
Former Material	Glass Fibre
Winding Depth	27.0 mm (1.05 in)
Magnetic Gap Depth	11.0 mm (0.43 in)
Flux Density	1.25 T

DESIGN

Surround Shape	Roll	
Cone Shape	Radial	
Magnet Material	Neodymium Inside Slug	
Spider	Double Silicone	
Pole Design	T-Pole	
Woofer Cone Treatment TWP Waterproof Both Sides		
Recommended Enclosu	re 160.0 dm ³ (5.65 ft ³)	
Recommended Tuning	29 Hz	

PARAMETERS⁴

Resonance Frequency	36 Hz
Re	5.1 Ω
Qes	0.49
Qms	5.0
Qts	0.44
Vas	83.0 dm ³ (2.93 ft ³)
Sd	855.0 cm ² (132.5 in ²)
ηο	0.8 %
Xmax	10.5 mm
Maximum Excursion	14.0 mm
Mms	240.0 g
Bl	23.0 Txm
Le	1.6 mH
EBP	73 Hz

MOUNTING AND SHIPPING INFO

Overall Diameter	393 mm (15.5 in)	
Bolt Circle Diameter	374 mm (14.7 in)	
Baffle Cutout Diameter	354.0 mm (13.9 in)	
Depth	189 mm (7.44 in)	
Flange and Gasket Thickne	24 mm (0.94 in)	
Air Volume Occupied by Driver $6.0 \text{dm}^3 (\text{0.21 ft}^3)$		
Net Weight	8.6 kg (18.9 lb)	
Shipping Units	1	
Shipping Weight	9.9 kg (21.83 lb)	
Shipping Box 425x425x224 mm (16.73x16.73x8.82 in)		

SERVICE KIT

RCK15BG1008

- 2 hours test made with continuous pink noise signal within the range Fs-10Fs. Power calculated on rated nominal impedance. Loudspeaker in free air.
 Power on Continuous Program is defined as 3 dB greater than the Nominal rating.
 Applied RMS Voltage is set to 2.83 V for 8 ohms Nominal Impedance.
 Thiele-Small parameters are measured after a high level 20 Hz sine wave preconditioning test.