



# 2" Ceramic Cone Tweeter


**Program Power** 90 W 8 Ohm Rated impedance 2''- 50 mm **Nominal diameter** Sensitivity (2,83V/1m) 91 dB

Voice coil diameter 0,55 in - 14 mm 500-20000 Hz **Frequency Range** 

### **SPECIFICATIONS**

Nominal Diameter	2''- 50 mm
Rated Impedance	8 Ohm
Nominal Power Handling <sup>1</sup>	35 W
Program Power <sup>2</sup>	90 W
Sensitivity <sup>3</sup>	91 dB
Frequency Range <sup>4</sup>	500-20000 Hz
Minimum Impedance	-
Flange material	-
Magnet Material	Ferrite
Diaphragm Material	Cellulose fiber
Diaphragm Shape	-
Surround	Cellulose fiber
Voice Coil Diameter	0,55 in - 14 mm
Voice Coil Winding Material	-
Voice Coil Former Material	Paper
Flux Densitry	-
Ferrofluid	No
Connection type	-
Recommended Crossover Frequency	-


## FREQUENCY RESPONSE AND IMPEDANCE CURVE 67



# T/S PARAMETERS

8	Ohn

December for many	F-	4500    -
Resonance frequency	Fs	1500 Hz
DC Resistance	Re	5,4 Ohm
Mechanical Q Factor	Qms	0
Electrical Q Factor	Qes	0
Total Q Factor	Qts	0
BI Factor	BI	2,1 Tm
Effective Moving Mass	Mms	0,35 g
Suspension Compliance	Cms	-
Effective Piston Diameter	D	0 -
Effective piston area	Sd	0 -
Voice Coil Inductance @ 1kHz	Le	0,08 mH



Overall Diameter	58x58 mm -
Baffle Cutout Diameter	50 mm - 1,97 in
Flange Thickness	0,8 mm - 0,03 in
Total Depth	24,8 mm - 0,98 in
Bolt Circle Diameter	161 mm - 6,34 in
Bolt Holes Quantity and Diameter	4 / 4,5 mm - 0,18 in
Net Weight	0,14 Kg - 0,31 lb
Shipping Units	12 Pcs

- Nominal power is determined according to AES2-1984 (r2003) standard.
  Program Power is defined as 3 dB greater than the Nominal rating.
  Sensitivity represents the averaged value of acoustic output as measured on the forward central axis of cone, at distance 1m, when connected to 2,83V sine wave test signal.
  Frequency range is given as the band of frequencies delineated by the lower and upper limits where the output level drops by 10 dB below the rated sensitivity in half space environment.
  Inear Math. Xmax is calculated as (Hvc-Hg)/2 + Hg/4 where Hvc is the coil depth and Hg is the gapdepth.
  Frequency response curve is measured on IEC Baffle.
  Impedance curve is measured in free air conditions at small signals.